



Box, FRP, 24"x24"x24", Tier 15

By QUAZITE
Catalog # [B14242424A](#)

Quazite® FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

| | |
|-------------------------|--------------------|
| Catalog Number | B14242424A |
| EU RoHS Indicator | No |
| Insulated? | No |
| Load Rating (ANSI Tier) | T15 |
| Material | Fiberglass |
| QuaziteFRP | Yes |
| Type | Below Ground Boxes |
| UPC | 662037179106 |



*Representative Image

Dimensions

| | |
|------------|-----------------------|
| Dimensions | 24 in x 24 in x 24 in |
| Height | 24 in |
| Length | 24 in |
| Weight | 96.6 lb |
| Width | 24 in |

Certifications And Compliance

Buy America(n) Qualified Contact Manufacturer

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Sales Drawings - Quazite Box Standard Version](#)
- [Specifications - B14242424A](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)