



Box, FRP, 24"x36"x24", Tier 22

By QUAZITE
Catalog # [B19243624A](#)

Quazite FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.



Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T22
Material	Fiberglass
Type	Below Ground Boxes
UPC	662037158125

Dimensions

Dimensions	36 in x 24 in x 24 in
Height	24 in
Length	36 in
Weight	119.7 lb
Width	24 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Sales Drawings - CDR 24 X 36 X 24 Box Standard Version \(B19243624A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-B19243624A-SPEC-EN | REV 1/2024