



Box, FRP, 30"x48"x18", Tier 8, Gaskets

By QUAZITE
Catalog # B1A304818G

Quazite FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T8
Material	Fiberglass
Type	Below Ground Boxes
UPC	066203715889
Weight Load Rating (Design/Test)	8,000/12,000 lb

Dimensions

Dimensions	48 in x 30 in x 18 in
Height	18 in
Length	48 in
Weight	190 lb
Width	30 in

Product Assets

[Catalogs - Underground Enclosures](#)

[Sales Drawings - Quazite 30 X 48 X 18 Box W/ Gasket Standard Version](#)

[Video - PenCell® Enclosures](#)

[Video - Hubbell Power Systems How to Install Small Enclosures](#)

[Video - Hubbell Power Systems How to Install Large Enclosures](#)



A Hubbell brand