



## Box, FRP, 30"x48"x24", Tier 15

By QUAZITE  
Catalog # [B1B304824A](#)

Quazite FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.



### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Material	Fiberglass
Type	Below Ground Boxes
UPC	662037159153
Weight Load Rating (Design/Test)	15,000/22,000 lb

### Dimensions

Dimensions	48 in x 30 in x 24 in
Height	24 in
Length	48 in
Weight	199 lb
Width	30 in

### Product Assets

- [Catalogs - Underground Enclosures \(CA07017E\\_UG\\_23\\_WEB\)](#)
- [Sales Drawings - Quazite 30 X 48 X 24 Box Standard Version \(B1B304824A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
QUAZ-B1B304824A-SPEC-EN | REV 1/2024