



Cover, FRP, Tier 15, 10"x15"

By QUAZITE
Catalog # C02101502A009



*Representative Image

Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	009
Logo Included?	Yes
Logo Text	Blank
Material	Fiberglass Reinforced Polymer
QuaziteFRP	Yes
UPC	662037180843
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	15 in x 10 in x 2 in
Height	2 in
Length	15 in
Weight	17.85 lb
Width	10 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 10 X 15 X 02 Cover Standard Version](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)



A Hubbell brand