



Cover, FRP, Tier 15, 11"x21"

By QUAZITE
Catalog # [C02112102A009](#)

Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Catalog Number	C02112102A009
EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Fiberglass Reinforced Polymer
QuaziteFRP	Yes
UPC	662037180867
Weight Load Rating	15,000/22,500 lb



*Representative Image

Dimensions

Dimensions	21 in x 11 in x 2 in
Height	2 in
Length	21 in
Weight	28.35 lb
Width	11 in

Certifications And Compliance

Buy America(n) Qualified Contact Manufacturer

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 11 X 21 X 002 Cover Standard Version](#)
- [Specifications - C02112102A009](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)