



Cover, FRP, Tier 8, 15"x17"

By QUAZITE
Catalog # C10151702A009

Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

| | |
|-------------------------|------------------|
| EU RoHS Indicator | No |
| Insulated? | No |
| Load Rating (ANSI Tier) | T8 |
| Material | Polymer Concrete |
| QuaziteFRP | Yes |
| UPC | 662037181550 |

Dimensions

| | |
|------------|----------------------|
| Dimensions | 17 in x 15 in x 2 in |
| Height | 2 in |
| Length | 17 in |
| Weight | 22 lb |
| Width | 15 in |

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)