



## Cover, FRP, Tier 15, 11"x18"

By QUAZITE  
Catalog # C12111802A017

Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	009
Logo Included?	Yes
Logo Text	Blank
Material	Fiberglass Reinforced Polymer
UPC	662037185701
Weight Load Rating (Design/Test)	15,000/22,500 lb

### Dimensions

Dimensions	18 in x 11 in x 2 in
Height	2 in
Length	18 in
Weight	24.15 lb
Width	11 in

### Product Assets

- [Catalogs - Underground Enclosures \(CA07017E\\_UG\\_23\\_WEB\)](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 11 X 18 X 02 Cover Standard Version \(C12111802A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
QUAZ-C12111802A017-SPEC-EN | REV 1/2024