



## Cover, FRP, Tier 15, 13"x24"

By QUAZITE  
Catalog # [C12132402A009](#)

Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Fiberglass Reinforced Polymer
UPC	662037185114
Weight Load Rating (Design/Test)	15,000/22,500 lb

### Dimensions

Dimensions	24 in x 13 in x 2 in
Height	2 in
Length	24 in
Weight	42 lb
Width	13 in

### Product Assets

- [Catalogs - Underground Enclosures \(CA07017E\\_UG\\_23\\_WEB\)](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite Cover \(C12132402A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
QUAZ-C12132402A009-SPEC-EN | REV 1/2024