



Round Cover, FRP, Tier 15, 20" Dia

By QUAZITE
Catalog # [C12200002A017](#)

Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

| | |
|----------------------------------|-------------------------------|
| Insulated? | No |
| Load Rating (ANSI Tier) | T15 |
| Logo Code | 009 |
| Logo Included? | Yes |
| Logo Text | Blank |
| Material | Fiberglass Reinforced Polymer |
| Weight Load Rating (Design/Test) | 15,000/22,500 lb |

Dimensions

| | |
|--------|----------|
| Weight | 24.15 lb |
| Width | 20 in |

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite ø20 X 2 Cover Standard Version \(C12200002A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-C12200002A017-SPEC-EN | REV 1/2024