



## Round Cover, FRP, Tier 15, 20" Dia

By QUAZITE

Catalog # C12320002A009

Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	046
Logo Included?	Yes
Logo Text	Traffic Signal
Material	Fiberglass Reinforced Polymer
QuaziteFRP	Yes
UPC	662037181987
Weight Load Rating (Design/Test)	15,000/22,500 lb

### Dimensions

Weight	111.3 lb
Width	32 in

### Product Assets

[Catalogs - Underground Enclosures](#)

[Literature - Quazite® FRP Cover Options \(Logos\)](#)

[Sales Drawings - Quazite ø32 Round Cover Standard Version](#)

[Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)

[Video - PenCell® Enclosures](#)

[Video - Hubbell Power Systems How to Install Large Enclosures](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
QUAZ-C12320002A009-SPEC-EN | REV 6/2024