



Cover, FRP, Tier 15, 36"x36"

By QUAZITE
Catalog # [C12363603A009](#)

Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	043
Logo Included?	Yes
Logo Text	Telephone
Material	Fiberglass Reinforced Polymer
UPC	662037182007
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	36 in x 36 in x 3 in
Height	3 in
Length	36 in
Weight	178.5 lb
Width	36 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 36 X 36 X 3 Cover Standard Version \(C12363603A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-C12363603A009-SPEC-EN | REV 1/2024