



Round Cover, FRP, Tier 15, 39" Dia

By QUAZITE

Catalog # C12390003A009

Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Fiberglass Reinforced Polymer
QuaziteFRP	Yes
UPC	662037182052
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Weight	262.5 lb
Width	39 in

Product Assets

[Catalogs - Underground Enclosures](#)

[Literature - Quazite® FRP Cover Options \(Logos\)](#)

[Sales Drawings - Quazite ø39 X 3 Cover Standard Version](#)

[Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)

[Video - PenCell® Enclosures](#)

[Video - Hubbell Power Systems How to Install Large Enclosures](#)



A Hubbell brand