



## Round Cover, FRP, Tier 15, 39" dia

By QUAZITE  
Catalog # C12390003A017

Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	021
Logo Included?	Yes
Logo Text	Fiber Optics
Material	Fiberglass Reinforced Polymer
UPC	066203719320
Weight Load Rating (Design/Test)	15,000/22,500 lb

### Dimensions

Dimensions	40.5 in x 39 in x 3 in
Height	3 in
Length	40.5 in
Weight	262.5 lb
Width	39 in

### Product Assets

- [Catalogs - Underground Enclosures](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite ø39 X 3 Cover Standard Version](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)
- [Video - Hubbell Power Systems PG3660 Retrofit Kit](#)