



Cover, FRP, Tier 22, 11"x18"

By QUAZITE

Catalog # C16111802A009



*Representative Image

Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T22
Logo Code	009
Logo Included?	Yes
Logo Text	Blank
Material	Polymer Concrete
QuaziteFRP	Yes
Weight Load Rating (Design/Test)	22,500/33,750 lb

Dimensions

Dimensions	18 in x 11 in x 2 in
Height	2 in
Length	18 in
Weight	24.15 lb
Width	11 in

Product Assets

[Catalogs - Underground Enclosures](#)

[Literature - Quazite® FRP Cover Options \(Logos\)](#)

[Sales Drawings - Quazite 11 X 18 X 02 Cover Standard Version](#)

[Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)

[Video - PenCell® Enclosures](#)

[Video - Hubbell Power Systems How to Install Large Enclosures](#)



A Hubbell brand