



## Cover, FRP, Tier 22, 13"x24"

By QUAZITE  
Catalog # C16132402A017



\*Representative Image

Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

Insulated?	No
Load Rating (ANSI Tier)	T22
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete
QuaziteFRP	Yes
Weight Load Rating (Design/Test)	22,500/33,750 lb

### Dimensions

Dimensions	24 in x 13 in x 2 in
Height	2 in
Length	24 in
Weight	42 lb
Width	13 in

### Product Assets

- [Catalogs - Underground Enclosures](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 13 X 24 X 02 Cover Standard Version](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)