



Cover, FRP, Tier 22, 24"x36"

By QUAZITE
Catalog # C16243603A009

Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T22
Logo Code	009
Logo Included?	Yes
Logo Text	Blank
Material	Polymer Concrete
UPC	662037182144
Weight Load Rating (Design/Test)	22,500/33,750 lb

Dimensions

Dimensions	36 in x 24 in x 3 in
Height	3 in
Length	36 in
Weight	98.7 lb
Width	24 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 24 X 36 X 03 Cover \(C16243603A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-C16243603A009-SPEC-EN | REV 1/2024