



Cover, FRP, Tier 15, 30"x60"

By QUAZITE
Catalog # C1B306003Y017

Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Catalog Number	C1B306003Y017
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Fiberglass Reinforced Polymer
QuaziteFRP	Yes
Weight Load Rating	15,000/22,500 lb

Dimensions

Dimensions	60 in x 30 in x 3 in
Height	3 in
Length	60 in
Weight	281.4 lb
Width	30 in

Product Assets

- [Catalogs - Underground Enclosures](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 30 X 60 X 3 One Piece Cover Standard Version](#)
- [Specifications - C1B306003Y017](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)



*Representative Image