



## Cover, FRP, Tier 15, 36"x60"

By QUAZITE  
Catalog # C1B366003A017



Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Fiberglass Reinforced Polymer
QuaziteFRP	Yes
Weight Load Rating (Design/Test)	15,000/22,500 lb

### Dimensions

Dimensions	60 in x 36 in x 3 in
Height	3 in
Length	60 in
Weight	349.65 lb
Width	36 in

### Product Assets

- [Catalogs - Underground Enclosures](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - CDR 36 X 60 X 3 Cover Standard Version](#)
- [Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)
- [Video - PenCell® Enclosures](#)
- [Video - Hubbell Power Systems How to Install Large Enclosures](#)