



## Cover, FRP, Tier 15, 48"x96"

By QUAZITE  
Catalog # C1B489603A009



Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Fiberglass Reinforced Polymer
UPC	662037182687
Weight Load Rating (Design/Test)	15,000/22,500 lb

### Dimensions

Dimensions	96 in x 48 in x 3 in
Height	3 in
Length	96 in
Weight	546 lb
Width	48 in

### Product Assets

[Catalogs - Underground Enclosures \(CA07017E\\_UG\\_23\\_WEB\)](#)  
[Literature - Quazite® FRP Cover Options \(Logos\)](#)  
[Sales Drawings - Quazite 48 X 96 X 03 Cover Standard Version \(C1B489603A\)](#)  
[Video - PenCell® How It's Made \(VI07068E0617\)](#)  
[Video - PenCell® Enclosures \(VI07062E0617\)](#)  
[Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
QUAZ-C1B489603A009-SPEC-EN | REV 1/2024