



Cover, FRP, Tier 22, 30"x48"

By QUAZITE
Catalog # C1C304803A017



Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T22
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete
Weight Load Rating (Design/Test)	22,500/33,750 lb

Dimensions

Dimensions	48 in x 30 in x 3 in
Height	3 in
Length	48 in
Weight	180.6 lb
Width	30 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite 30 X 48 X 3 Cover Standard Version \(C1C304803A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-C1C304803A017-SPEC-EN | REV 1/2024