



Cover, FRP, Tier 22, 30"x60"

By QUAZITE
Catalog # C1C306003A017



Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T22
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete
Weight Load Rating (Design/Test)	22,500/33,750 lb

Dimensions

Dimensions	60 in x 30 in x 3 in
Height	3 in
Length	60 in
Weight	281.4 lb
Width	30 in

Product Assets

[Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
[Literature - Quazite® FRP Cover Options \(Logos\)](#)
[Sales Drawings - CDR 30 X 60 X 3 Cover Standard Version \(C1C306003A\)](#)
[Video - PenCell® How It's Made \(VI07068E0617\)](#)
[Video - PenCell® Enclosures \(VI07062E0617\)](#)
[Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-C1C306003A017-SPEC-EN | REV 1/2024