



## Cover, FRP, Tier 22, 36"x60"

By QUAZITE  
Catalog # C1C366003A009



Quazite FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T22
Logo Code	012
Logo Included?	Yes
Logo Text	Communications
Material	Polymer Concrete
UPC	662037182731
Weight Load Rating (Design/Test)	22,500/33,750 lb

### Dimensions

Dimensions	60 in x 36 in x 3 in
Height	3 in
Length	60 in
Weight	349.65 lb
Width	36 in

### Product Assets

[Catalogs - Underground Enclosures \(CA07017E\\_UG\\_23\\_WEB\)](#)  
[Literature - Quazite® FRP Cover Options \(Logos\)](#)  
[Sales Drawings - Quazite 36 X 60 X 3 Cover Standard Version \(C1C366003A\)](#)  
[Video - PenCell® How It's Made \(VI07068E0617\)](#)  
[Video - PenCell® Enclosures \(VI07062E0617\)](#)  
[Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
QUAZ-C1C366003A009-SPEC-EN | REV 1/2024