



## Cover, FRP, Tier 22, 36"x72"

By QUAZITE

Catalog # C1C367203A009



Quazite® FRP ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete ring and cover in a multitude of sizes with a vast array of options allowing customization for any application.

\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T22
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete
QuaziteFRP	Yes
UPC	662037182748
Weight Load Rating (Design/Test)	22,500/33,750 lb

### Dimensions

Dimensions	72 in x 36 in x 3 in
Height	3 in
Length	72 in
Weight	372.75 lb
Width	36 in

### Product Assets

[Catalogs - Underground Enclosures](#)

[Literature - Quazite® FRP Cover Options \(Logos\)](#)

[Sales Drawings - Quazite 36 X 72 X 03 Cover Standard Version](#)

[Video - Hubbell Power Systems In Depth: ANSI vs AASHTO](#)

[Video - PenCell® Enclosures](#)

[Video - Hubbell Power Systems How to Install Large Enclosures](#)



A Hubbell brand