



Extension, FRP, 24"x36"x16", Tier 8

By QUAZITE
Catalog # [E00243616A](#)

Quazite ANSI/SCTE 77 certified enclosure boxes, feature a high quality polymer concrete construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T8
Material	Fiberglass-Reinforced Polymer
Type	Below Ground Box Extensions
UPC	662037158293

Dimensions

Dimensions	36 in x 24 in x 16 in
Height	16 in
Length	36 in
Weight	57.75 lb
Width	24 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Sales Drawings - Quazite 24 X 36 X 16 Bottom Extension Standard Version \(E00243616A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
QUAZ-E00243616A-SPEC-EN | REV 9/2023