



## Extension, FRP, 48"x96"x24", Tier 8

By QUAZITE  
Catalog # [EOA489624A](#)

Quazite ANSI/SCTE 77 certified enclosure boxes, feature a high quality polymer concrete construction in a multitude of sizes and depths allowing customization for any application.



\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T8
Material	Fiberglass-Reinforced Polymer
Type	Below Ground Box Extensions
UPC	662037164942

### Dimensions

Dimensions	96 in x 48 in x 24 in
Height	24 in
Length	96 in
Weight	311 lb
Width	48 in

### Product Assets

- [Catalogs - Underground Enclosures \(CA07017E\\_UG\\_23\\_WEB\)](#)
- [Sales Drawings - Quazite 48 X 96 X 24 Extension Standard Version \(EOA489624A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
QUAZ-EOA489624A-SPEC-EN | REV 1/2024