



## Extension, FRP, 48"x96"x36", Tier 15

By QUAZITE  
Catalog # [EOB489636A](#)

Quazite ANSI/SCTE 77 certified enclosure boxes, feature a high quality polymer concrete construction in a multitude of sizes and depths allowing customization for any application.



\*Representative Image

### Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

### General

Insulated?	No
Load Rating (ANSI Tier)	T15
Material	Fiberglass-Reinforced Polymer
Type	Below Ground Box Extensions

### Dimensions

Dimensions	96 in x 48 in x 36 in
Height	36 in
Length	96 in
Weight	317 lb
Width	48 in

### Product Assets

- [Catalogs - Underground Enclosures \(CA07017E\\_UG\\_23\\_WEB\)](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - Quazite 48 X 96 X 36 Extension Standard Version \(EOB489636A\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
QUAZ-EOB489636A-SPEC-EN | REV 1/2024