



Extension, FRP, 78"x96"x36", Tier 15, Solid Bottom

By QUAZITE
Catalog # EOB789636B

Quazite FRP ANSI/SCTE 77 certified enclosure boxes, feature a high quality and lightweight fiberglass construction in a multitude of sizes and depths allowing customization for any application.



*Representative Image

Features

- Combination of fiberglass base and polymer concrete ring and cover
- Lightweight and durable
- Fire and chemical resistant
- Multiple styles and sizes available

General

Insulated?	No
Load Rating (ANSI Tier)	T15
Material	Fiberglass-Reinforced Polymer
Type	Below Ground Box Extensions
UPC	066203716604

Dimensions

Dimensions	96 in x 78 in x 36 in
Height	36 in
Length	96 in
Weight	1137 lb
Width	78 in

Product Assets

[Catalogs - Underground Enclosures](#)

[Sales Drawings - Quazite 78 X 96 X 36 Extension W/ Integral Bottom Standard Version](#)

[Video - PenCell® Enclosures](#)

[Video - Hubbell Power Systems How to Install Small Enclosures](#)

[Video - Hubbell Power Systems How to Install Large Enclosures](#)