



Cover, Polymer Concrete, Tier 15, 13"x24", Gaskets

By QUAZITE
Catalog # [PG1324HG0009](#)

Quazite ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete construction in a multitude of sizes with a vast array of options allowing customization for any application.



*Representative Image

Features

- Stronger and lighter weight than regular concrete
- Cost effective
- Durable and long lasting
- Fire and chemical resistant
- Standard sizes are UL certified
- ANSI/SCTE77 certified
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	009
Logo Included?	Yes
Logo Text	Blank
Material	Polymer Concrete
UPC	662037140205
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	24 in x 13 in x 2 in
Height	2 in
Length	24 in
Weight	51 lb
Width	13 in

Product Assets

- [Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
- [Literature - Quazite® FRP Cover Options \(Logos\)](#)
- [Sales Drawings - Quazite Cover \(PG1324HG00\)](#)
- [Video - PenCell® How It's Made \(VI07068E0617\)](#)
- [Video - PenCell® Enclosures \(VI07062E0617\)](#)
- [Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-PG1324HG0009-SPEC-EN | REV 1/2024