



Cover, Polymer Concrete, Tier 15, 24"x36", Gaskets

By QUAZITE
Catalog # [PG2436HS0009](#)



Quazite ANSI/SCTE 77 certified enclosure covers feature a strong and durable polymer concrete construction in a multitude of sizes with a vast array of options allowing customization for any application.

Features

- Stronger and lighter weight than regular concrete
- Cost effective
- Durable and long lasting
- Fire and chemical resistant
- Standard sizes are UL certified
- ANSI/SCTE77 certified
- Multiple styles and sizes available

General

EU RoHS Indicator	No
Insulated?	No
Load Rating (ANSI Tier)	T15
Logo Code	017
Logo Included?	Yes
Logo Text	Electric
Material	Polymer Concrete
UPC	662037156244
Weight Load Rating (Design/Test)	15,000/22,500 lb

Dimensions

Dimensions	36 in x 24 in x 3 in
Height	3 in
Length	36 in
Weight	126.56 lb
Width	24 in

Product Assets

[Catalogs - Underground Enclosures \(CA07017E_UG_23_WEB\)](#)
[Literature - Quazite® FRP Cover Options \(Logos\)](#)
[Sales Drawings - Quazite 24 X 36 Cover Standard Version \(PG2436HS00\)](#)

[Video - PenCell® How It's Made \(VI07068E0617\)](#)

[Video - PenCell® Enclosures \(VI07062E0617\)](#)

[Video - Hubbell Power Systems How to Install Small Enclosures \(VI0750E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
QUAZ-PG2436HS0009-SPEC-EN | REV 1/2024