



3/4 in. Rigid/IMC Locknut

By Raco
Catalog # 1003

3/4 in. Rigid/IMC Locknut



*Representative Image

Features

- All steel construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- For use in dry locations
- UL and CSA Listed
- Available in trade sizes 1/2 in. through 6 in.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Locknuts
Material	Steel
UPC	050169010037

Dimensions

Dimensions	0.172 in x 1.422 in x 1.422 in
Height	1.422 in
Length	0.172 in
Trade Size	3/4 in
Weight	0.02 lb
Width	1.422 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1000
Minimum Pack Quantity	100
Pallet Quantity	75000

Product Assets

[Brochures - HCC Products for Solar](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195969-1](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1003-SPEC-EN | REV 6/2024