



## 3-1/2 in. Rigid/IMC Locknut

By Raco  
Catalog # 1014

3-1/2 in. Rigid/IMC Locknut



\*Representative Image

### Features

- All steel construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- For use in dry locations
- UL and CSA Listed
- Available in trade sizes 1/2 in. through 6 in.

### Application

For use in dry locations on threaded rigid/IMC conduit to secure conduit to a box or enclosure

### General

Conduit Type	Rigid/IMC
Fitting Type	Locknuts
Material	Steel
UPC	050169010143

### Dimensions

Dimensions	0.17 in x 4.75 in x 4.75 in
Height	4.75 in
Length	0.17 in
Trade Size	3-1/2 in
Weight	0.179 lb
Width	4.75 in

### Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	5040

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195969-1](#)  
[Product Logo - Conduit](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-1014-SPEC-EN | REV 6/2024