



3/4 in. Rigid/IMC Bushing

By Raco
Catalog # 1103

3/4 in. Rigid/IMC Bushing



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Application	For use on threaded rigid/IMC conduit to provide a smooth rounded surface at the entrance of raceways
Conduit Type	Rigid/IMC
Fitting Type	Bushings
Insulation Type	Uninsulated
Material	Malleable Iron
UPC	050169011034

Dimensions

Dimensions	0.563 in x 1.406 in x 1.406 in
Height	1.406 in
Length	0.563 in
Trade Size	3/4 in
Weight	0.074 lb
Width	1.406 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	25200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-1103-SPEC-EN | REV 6/2024