



2 in. Rigid/IMC Bushing

By Raco
Catalog # 1108

2 in. Rigid/IMC Bushing



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Application	For use on threaded rigid/IMC conduit to provide a smooth rounded surface at the entrance of raceways
Conduit Type	Rigid/IMC
Fitting Type	Bushings
Insulation Type	Uninsulated
Material	Malleable Iron
UPC	050169011089

Dimensions

Dimensions	0.719 in x 2.719 in x 2.719 in
Height	2.719 in
Length	0.719 in
Trade Size	2 in
Weight	0.352 lb
Width	2.719 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	50
Pallet Quantity	4800

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand