



2-1/2 in. Rigid/IMC Bushing

By Raco
Catalog # 1110

2-1/2 in. Rigid/IMC Bushing



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Uninsulated
Material	Malleable Iron
UPC	050169011102

Dimensions

Dimensions	0.938 in x 3.281 in x 3.281 in
Height	3.281 in
Length	0.938 in
Trade Size	2-1/2 in
Weight	0.368 lb
Width	3.281 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	30
Minimum Pack Quantity	30
Pallet Quantity	6300

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand