



3-1/2 in. Rigid/IMC Bushing

By Raco
Catalog # 1114

3-1/2 in. Rigid/IMC Bushing

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

Application

For use on threaded rigid/IMC conduit to provide a smooth rounded surface at the entrance of raceways

General

Catalog Number	1114
Conduit Type	Rigid/IMC
Fitting Type	Bushings
Insulation Type	Uninsulated
Material	Malleable Iron
UPC	050169011140

Dimensions

Dimensions	0.938 in x 4.406 in x 4.406 in
Height	4.406 in



*Representative Image

Length	0.938 in
Trade Size	3-1/2 in
Weight	0.8 lb
Width	4.406 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3200

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - Conduit](#)
- [SDS - HCC SDS](#)
- [Specifications - 1114](#)
- [Terms and Conditions - HCC Terms & Conditions](#)