



4 in. Rigid/IMC Bushing

By Raco
Catalog # 1116

4 in. Rigid/IMC Bushing

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

Application

Rigid

General

Catalog Number	1116
Compatibility	GRC
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Uninsulated
Material	Malleable Iron
Paintable/Stainable	No
UPC	050169011164

Dimensions

Dimensions	0.938 in x 4.906 in x 4.906 in
Height	4.906 in



*Representative Image

Length	0.938 in
Trade Size	4 in
Weight	1.12 lb
Width	4.906 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	2100

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - Conduit](#)
- [SDS - HCC SDS](#)
- [Specifications - 1116](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand