



3-1/2 in. Octagon Box, Drawn, 1-1/2 in. Deep, Three 1/2 in. KO's & NMSC Clamps

By Raco
Catalog # 112

3-1/2 in. Octagon Box, Drawn, 1-1/2 in. Deep, Three 1/2 in. KO's & NMSC Clamps



Features

- Drawn steel construction
- 3-1/2 in. x 1-1/2 in. deep
- L clamps provided for non-metallic sheathed cable (NMSC)
- Supplied with three 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 11.8 cu. in. capacity

General

Bracket Type	No Bracket
Catalog Number	112
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	3.5 in
Type	Box
UPC	050169001127
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	1.563 in
Cubic Capacity	11.8 cu.in
Depth	1.5 in
Fixture Lbs.	50 lb
Height	3.5 in
Raised Ground	No
Weight	0.459 lb
Width	3.5 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	3150

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-112-SPEC-EN | REV 6/2024