



2-1/2 in. Rigid/IMC Bushing, Insulated

By Raco
Catalog # 1126

2-1/2 in. Rigid/IMC Bushing, Insulated

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Catalog Number	1126
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169011263

Dimensions

Dimensions	0.938 in x 3.281 in x 3.281 in
Height	3.281 in
Length	0.938 in
Trade Size	2-1/2 in



*Representative Image

Weight	0.378 lb
Width	3.281 in

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	4950

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Specifications - 1126](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand