



3 in. Rigid/IMC Bushing, Insulated

By Raco
Catalog # 1127

3 in. Rigid/IMC Bushing, Insulated



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Catalog Number	1127
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169011270

Dimensions

Dimensions	0.938 in x 3.875 in x 3.875 in
Height	3.875 in
Length	0.938 in
Trade Size	3 in
Weight	0.444 lb
Width	3.875 in

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	3240

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-1127-SPEC-EN | REV 6/2024