



4 in. Rigid/IMC Bushing, Insulated

By Raco
Catalog # 1129

4 in. Rigid/IMC Bushing, Insulated



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

| | |
|-------------------|----------------------|
| Catalog Number | 1129 |
| Conduit Type | Rigid/IMC |
| EU RoHS Indicator | Contact Manufacturer |
| Fitting Type | Bushings |
| Insulation Type | Insulated |
| Material | Malleable Iron |
| UPC | 050169011294 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 0.938 in x 4.906 in x 4.906 in |
| Height | 4.906 in |
| Length | 0.938 in |
| Trade Size | 4 in |
| Weight | 1.07 lb |
| Width | 4.906 in |

Certifications And Compliance

| | |
|----------------------|---------------|
| Certified Listed | UL Listed |
| | CSA Certified |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 5 |
| Minimum Pack Quantity | 5 |
| Pallet Quantity | 1600 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-1129-SPEC-EN | REV 6/2024