



## 1-1/4 in. Rigid/IMC Bushing, Insulated

By Raco  
Catalog # 1135

1-1/4 in. Rigid/IMC Bushing, Insulated



\*Representative Image

### Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

### General

Catalog Number	1135
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169011355

### Dimensions

Dimensions	0.656 in x 2.125 in x 2.125 in
Height	2.125 in
Length	0.656 in
Trade Size	1-1/4 in
Weight	0.09 lb
Width	2.125 in

### Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	15750

### Product Assets

[Brochures - HCC Products for Solar](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-1135-SPEC-EN | REV 6/2024