



1-1/2 in. Rigid/IMC Bushing, Insulated

By Raco
Catalog # 1136

1-1/2 in. Rigid/IMC Bushing, Insulated



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169011362

Dimensions

Dimensions	0.719 in x 2.344 in x 2.344 in
Height	2.344 in
Length	0.719 in
Trade Size	1-1/2 in
Weight	0.256 lb
Width	2.344 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7875

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1136-SPEC-EN | REV 6/2024