



# 2 in. Rigid/IMC Bushing, Insulated

By Raco  
Catalog # 1138

2 in. Rigid/IMC Bushing, Insulated

## Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

## General

Catalog Number	1138
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Item Type	4D
Material	Malleable Iron
UPC	050169011386

## Dimensions

Dimensions	0.719 in x 2.719 in x 2.719 in
Height	2.719 in
Length	0.719 in



\*Representative Image

Trade Size	2 in
Weight	0.34 lb
Width	2.719 in

## Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	6300

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Specifications - 1138](#)  
[Terms and Conditions - HCC Terms & Conditions](#)