



3-1/2 in. Octagon Box, Drawn, 1-1/2 in. Deep, Three 1/2 in. KO's & NMSC Clamps, TS Bracket

By Raco
Catalog # 119

3-1/2 in. Octagon Box, Drawn, 1-1/2 in. Deep, Three 1/2 in. KO's & NMSC Clamps, TS Bracket



Features

- Drawn steel construction with "TS" side-mount bracket with gauging tabs and recessed nailing spurs
- 3-1/2 in. x 1-1/2 in. deep
- L clamps provided for non-metallic sheathed cable (NMSC)
- Supplied with two 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 11.8 cu. in. capacity

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	3.5 in
Type	Box
UPC	050169001196
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	1.563 in
Cubic Capacity	11.8 cu.in
Depth	1.5 in
Fixture Lbs.	50 lb
Height	7 in
Raised Ground	No
Weight	0.558 lb
Width	3.625 in

Certifications And Compliance

Certified Listed	UL Listed
Prop 65 Chemicals	Hexavalent Chromium

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	2100

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-119-SPEC-EN | REV 6/2024