



## 3-1/2 in. Rigid/IMC Sealing Locknut

By Raco  
Catalog # 1210

3-1/2 in. Rigid/IMC Sealing Locknut



\*Representative Image

### Features

- All steel construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- Economical alternative to a threaded enclosure connector
- UL and CSA Listed
- Available in trade sizes 1/2 in. through 4 in.

### General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Locknuts
Item Type	4D
Material	Steel
UPC	050169012109

### Dimensions

Dimensions	0.169 in x 4.75 in x 5.75 in
Height	5.75 in
Length	0.169 in
Trade Size	3-1/2 in
Weight	0.222 lb
Width	4.75 in

### Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	3675

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195969-1](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-1210-SPEC-EN | REV 6/2024