



3/4 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

By Raco
Catalog # 1213



*Representative Image

3/4 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #4 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in through 4 in.

General

Conduit Type	Rigid/IMC
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169012130

Dimensions

Dimensions	0.75 in x 1.406 in x 1.782 in
Height	1.782 in
Length	0.75 in
Trade Size	3/4 in
Weight	0.1 lb
Width	1.406 in

Electrical Ratings

Grounding Wire Capacity Maximum	#4 STR
Grounding Wire Capacity Minimum	#14 SOL

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	15000

Product Assets

[Brochures - HCC Products for Solar](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC-E195975-1](#)
[Product Logo - Conduit](#)
[Sales Drawings - GROUND BUSHING WITH GROUNDING LUG CUS](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1213-SPEC-EN | REV 6/2024