



1 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

By Raco
Catalog # 1214

1 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug,
Insulated

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #4 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in through 4 in.

General

Catalog Number	1214
Conduit Type	Rigid/IMC
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169012147

Dimensions

Dimensions	0.969 in x 1.75 in x 2.125 in
Height	2.125 in
Length	0.969 in
Trade Size	1 in
Weight	0.134 lb
Width	1.75 in



*Representative Image

Electrical Ratings

Grounding Wire Capacity Maximum	#4 STR
Grounding Wire Capacity Minimum	#14 SOL

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	50
Pallet Quantity	16000

Product Assets

[Brochures - HCC Products for Solar](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC-E195975-1](#)
[Product Logo - Conduit](#)
[Sales Drawings - 1214 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 1214](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand