



1-1/4 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

By Raco
Catalog # 1215



*Representative Image

1-1/4 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #4 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in through 4 in.

General

| | |
|-------------------|----------------------|
| Catalog Number | 1215 |
| Conduit Type | Rigid/IMC |
| Connector Type | Grounding |
| EU RoHS Indicator | Contact Manufacturer |
| Fitting Type | Bushings |
| Insulation Type | Insulated |
| Material | Malleable Iron |
| UPC | 050169012154 |

Dimensions

| | |
|------------|------------------------------|
| Dimensions | 1.281 in x 2.125 in x 2.5 in |
| Height | 2.5 in |
| Length | 1.281 in |
| Trade Size | 1-1/4 in |
| Weight | 0.169 lb |

Width 2.125 in

Electrical Ratings

| | |
|---------------------------------|---------|
| Grounding Wire Capacity Maximum | #4 STR |
| Grounding Wire Capacity Minimum | #14 SOL |

Certifications And Compliance

| | |
|---|--|
| Buy American Compliant Certified Listed | Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|----|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 25 |

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC-E195975-1](#)
- [Product Logo - Conduit](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)