



# 1-1/2 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

By Raco  
Catalog # 1216

1-1/2 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

## Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #4 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in through 4 in.

## General

Catalog Number	1216
Conduit Type	Rigid/IMC
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169012161

## Dimensions

Dimensions	1.5 in x 2.344 in x 2.719 in
Height	2.719 in
Length	1.5 in
Trade Size	1-1/2 in
Weight	0.271 lb
Width	2.344 in



\*Representative Image

## Electrical Ratings

Grounding Wire Capacity	#4 STR
Maximum	
Grounding Wire Capacity	#14 SOL
Minimum	

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	6300

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Certifications - UL COC-E195975-1](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Specifications - 1216](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand